



Gravimetric Doser

SGD



SGD Series

■ Coding Principle



■ Features

- Chrome coating dosing screw for extended durability.
- Servo motor to ensure fast response, smooth feeding, and precision dosing.
- Modular design for easy to disassemble, easy to clean, and replace.
- Material purge cleaning for easy replacement of masterbatch.
- Uninterrupted by power failure, and resume operation after power recovery.
- The unit is data communication ready via ethernet Modbus TCP.
- Support data export function to check production status.
- Dosing control through loss-it-weight technology for satisfying high dosing precision needs.



SGD-D



Parameter Setting Mode




Recipe Edit Menu


■ Application

The servo-driven SGD series gravimetric doser is controlled by PLC. It is suitable for injection moulding and extrusion occasions, which require a precision dosing ratio with masterbatch, additive, virgin, or regrind. SGD can work with the VL - Venturi Loader to realize the auto conveying of the masterbatch to the dosing unit. The unit is also available in dual doser.




Working Principle





Outline Drawings



SGD Series

■ Specifications


		SGD	SGD-D	
Motor Power (kW)		0.4	0.4 × 2	
Screw External Dia.(mm)		16	16	
Output Capacity (kg/hr)		0.1~32	0.1~64	
Sto	orage Hopper (L)	10	10	
Dimensions	H(mm)	510	510	
	W(mm)	720	1196	
	D(mm)	536	536	
Weight(kg)		37	56	

Notes:1) The outputs of the above models are measured under the conditions of 1.0 kg/L bulk density and masterbatch in diameter of 2-3mm in continuous operation. Actual output capacity may vary due to bulk density, flow ability, granule size, and recipe ratio.

- 2) When the master batch hopper is mounted with the auto conveying device, the total weight of the hopper shall not exceed 25KG (including the master batch).
- 3) Power: 1Φ, 230VAC, 50Hz.

Accessories


Mixer CMB-1 enhances the mixing uniformity



Model	Motor Power (kW)	H(mm)	W(mm)	D(mm)	Weight(kg)
CMB-1	0.25	364	347	371	16

Power: 34, 400VAC, 50Hz


 The collective hopper SCH-12U is the main material hopper, makes easy for users to add the main material.




Heavy base (Used with SHE-E/SEHD-75~300 or SHD-160U~SHD-450U)











Size of the heavy base


Model	H(mm)	D(mm)	W(mm)	Weight(kg)
HB-1	332	374	374	21
HB-2	527	374	374	25

Notes: When collocating with standard SGD, the model is HB-1. When collocating with standard SCM+CMB-1, the model is HB-2.

Work with a large drying hopper with a heavy base and auto conveying.







Mount hole of hopper adapter

Model	H(mm)	D(mm)	W(mm)	Weight(kg)
НТВ	225	275	525	5.2

Shini Group

Addr: No. 23, Minhe St., Shulin Dist., New Taipei, Taiwan

Tel: +886 2 2680 9119

Fax: +886 2 2680 9229

Email: shini@shini.com

Factories:

- Taiwan
- Dongguan
- Pinghu
- Ningbo
- Chongqing
- Pune

2022-10-15-04 Copyrights Reserved.